




Shown with
Optional Sensor (Not Included)

DIMENSIONS:

23-3/4"(L) x 15-1/8"(W) x 2-7/8"(H)



LLHB2-100W-40K-D
LLHB2-100W-50K-D

LED LINEAR HIGH BAYS

Ideal for one-for-one replacement of conventional lighting systems such as HID and fluorescent. Applications include manufacturing, warehousing and other large indoor spaces with mounting heights from 10 ft. to 40 ft. Luminaire shall be suspended at a minimum 24 inches from the ceiling.

ELECTRICAL SPECIFICATIONS:

- Voltage: 120~277 VAC/50~60 Hz
- Wattage: 100 W
- Power factor: >0.9
- Efficacy: 140LM/W

HOUSING SPECIFICATIONS:

- Slim Aluminum
- Aluminum LED board
- Operating temperature: -40°F ~ 122°F

CERTIFICATIONS: UL, DLC



WARRANTY: 7 years




3.5 FT. Adjustable Suspension Kit
With Ceiling Mount Disks (Included)



Surface Mounting Kit
(Included)

MODEL	WATTS	VOLTAGE	LUMENS	COLOR TEMP
LLHB2-100W-40K-D	100W	100~277V AC	14000 LM	4000K
LLHB2-100W-50K-D	100W	100~277V AC	14000 LM	5000K

PHOTOMETRICS:



LIGHTING SPECIFICATIONS:

- Dimming: 0~10V dimmable
- LED: Optical Polycarbonate Lens
- LED: LUMILEDS LED 140 LM/W
- Total lumens: 14000 LM
- Color temperature: 4000K & 5000K
- Color rendering index: >80
- Beam angle: 90°

