


LRX-20-50W-MCTP

POWER & CCT BARN/AREA LIGHT









Customer Name:

Project Name:

Note:

Type:





9 1/2"(W) x 13 1/2"(H)

Features

- Back plate: Die-cast aluminum
- Polycarbonate Lens

- 7-Year Warranty
- Multi CCT, Switch is on bottom of Fixture

Technical Specifications

Electrical:

Voltage: 120-277V AC 60HzWattage: 20W/ 30W/ 40W/ 50W

Power Factor: >0.90Efficacy: 130 LPWTHD: <20%

Mechanical:

- Die-Cast ADC12 Aluminum Alloy, Outdoor Powder Coated
- Lens: High light Transmittance PC, Anti-UV and Fire Resistant
- 1-1/4" EMT Elbow & Mounting Strap Included
- NEMA Twist-Lock Photocell Included
- Aluminum LED board: High Conductive, Waterproof, Aging Resistance, Salt Resistance
- Operating Temperature: -4°F to 104°F
- Wet Location
- 7-Year Warranty
- IP44

Lighting:

Dimming: 0-10V DimmingTotal Lumens: 6500LM

· Multi CCT, Switch is on bottom of Fixture

Color Temperatures: 3000K/ 4000K/ 5000K/ 5700K

Color Rendering Index: CRI ≥ 70

Beam Angle: 90° x 110°
Rated life: 70,000 Hrs

Applications:

• LED Dusk to Dawn Light with Photocell ideal for general site lighting, yarn/barn lighting, loading docks, doorway, pathway and parking areas.















Photometrics: LRX-20-50W-MCTP





Other Views:







Front View



Back View

Performance Table: LRX-20-50W-MCTP

MODEL NO.	Wattage	Voltage	Lumens	Color Temp.	BUG Rating	LPW
LRX-20-50W-MCTP	20W 30W 40W 50W	120-277V	2600LM 3900LM 5200LM 6500LM	3000K 4000K 5000K 5700K	B2-U3-G1	130

Sample Ordering

Model	Min. Watt		t	Max. Wat	Color Temp.	
LRX		20		50	MCTP	

ACCESSORIES:



90° EMT Arm and Wall Bracket (Mounting Strap) included

Arm Diameter: 1-1/4" EMT Elbow



