

JOB NAME: \_\_\_\_\_

DATE: \_\_\_\_\_

TYPE: \_\_\_\_\_



**ACCESSORIES:**



**SDL4-BF-2700K SDL4-BF-3000K**  
**SDL4-BF-4100K SDL4-BF-5000K**

**LED Trims (Baffle Trim) - 4" square**

Isolated driver for improved thermal management.

MODEL NO	WATTAGE	LUMENS	VOLTAGE	COLOR TEMP
SDL4-BF-2700K	9W	600	120V AC	WW 2700K
SDL4-BF-3000K	9W	650	120V AC	WW 3000K
SDL4-BF-4100K	9W	700	120V AC	NW 4100K
SDL4-BF-5000K	9W	750	120V AC	DL 5000K

**ELECTRICAL SPECIFICATIONS:**

- Voltage: 120V AC
- Wattage: 13W
- Other wattages available: 11W 4"
- Power factor: 90% +

**LIGHTING SPECIFICATIONS:**

- LED type/brand: EPISTAR chip (COB) and Driver-35,000-hour design life
- Dimmable: Yes
- Color temperature: 2700K and 3000K (Warm white), 4100K(Natural white), 5000K (Daylight)
- CRI: 90

**OTHERS:**

- Net weight: 0.76lbs / 345g
- Gross weight per CTN: 43.65lbs / 19.8kg

**HOUSING SPECIFICATIONS:**

- Housing: Spun aluminum with white powder coat finish
- Trim ring: Integrated spun aluminum white powder coat finish
- Gasket: Close cell Neoprene foam gasket
- Lens: 0.125" white translucent acrylic
- Wet locations: Suitable for damp locations
- Maximum ambient 4 °C (104 °F)

**CERTIFICATIONS:**

- UL listed

**WARRANTY:**

- Five-year warranty

