WA SERIES


Commercial Indoor Lighting



WA-4FT-30W-MCT-D



The LED Wrap-Around Light is a cost-effective, energy-efficient utility lighting fixture for surface-mount applications such as corridors, stairwells, public rooms, schools, hospitals, and utility areas.



Features

- LED Architectural Wrap-Around Lights
- White Finish
- Light Source: High-lumen LEDs
- 5-Year Warranty

- 50.000 Hours Rated Life
- Lens: Opal Polycarbonate
- MCT: Multi Color Temperature (Selectable with Switch Inside Fixture)

Technical Specifications

Electrical:

Voltage: 120-277VAC 50/60Hz

Wattage: 30WPower Factor: >0.95Efficacy: 98/ 98/ 105 LPW

Mechanical:

- White Finish
- Housing: Die-formed Heavy Gauge Cold Rolled Steel with Powder-Coated White
- Steel Thickness: 24 Gauge
- Driver: Optional
- Installation: Ceiling-Mounted
- Optional Battery Backup Available for 30W Units
- Operating Temp: -22°F~107°F
- Suitable for Damp Locations

Lighting:

- Dimmable: 0~10V Dimming
- Total Lumens: 3166LM/ 3217LM/ 3340LMColor Temperatures: 3500K/4000K/5000K
- Multi-CCT (selectable with switch inside the fixture)
- Color Rendering Index: CRI ≥ 82
- IP Rating: IP40

Applications:

 Ideal for corridors, stairwells, public rooms, schools, hospitals, and utility areas
















Photometrics: WA-4FT-MCT







Other Views:







Front View Side View Back View

Performance Table: WA-4FT-MCT

MODEL NO.	Wattage	Voltage	Lumens	Color Temp.	BUG Rating	LPW
WA-4FT-30W-MCT-D	30W	120~277V	3166LM 3217LM 3340LM	3500K 4000K 5000K	B2-U3-G1	98 98 105

Sample Ordering

Model			Size		Wattage		Color Temp. Feature			
	WA	-	4FT	_	30W	_	MCT	_	D	

Factory-Installed Options:

Blank = No Option For Accessories
OPT-EM-CM1INT= INTERNAL EMERGENCY BACKUP BATTERY
OPT-SEN-2MDR-36=PROGRAMMABLE MICROWAVE BI-LEVEL SENSOR
WEC-3RC=OPTIONAL REMOTE CONTROL
OPT-2P-58=PIR SENSOR (not remote capable)

Example:

1. WA-4FT-30W-MCT-D (FOR WA 4FT 30W MCT FIXTURE 120-277V)

2. WA-4FT-30W-MCT-D (FOR WA 4FT 30W MCT FIXTURE 120-277V)
OPT-EM-CM1INT (INTERNAL EMERGENCY BACKUP BATTERY)

SENSOR AND EMERGENCY BATTERY BACKUP OPTIONS:





OPT-EM-CM1INT OPT-SEN-2MDR-36





WEC-3RC

OPT-2P-58



