

Destroy private documents and materials with the Royal Sovereign 120 sheet Auto-Feed, Cross-Cut Shredder.



Highlights

- **Efficiency:** Auto-Feed can shred 120 sheets. Manual Feed can shred 5 sheets.
- **Quiet Operation:** Operates under 65 dB.
- **Security:** Uses P-4 level cross-cut security to shred particles sized 4 x 28 mm.
- **Safety:** Features overheat protection and auto-reverse to assist with jams.
- **Easy Maintenance:** Bin full indicator will notify user when to empty the basket.
- **Portability:** Includes attachable easy-gliding caster wheels.
- **Eco-Friendly:** cTUVus listed.

Perfect hands-free shredder solution for your home or office!

RAF-25P



120 SHEET
CAPACITY

6.6 GALLON
BASKET

P-4 LEVEL
SECURITY



SPECIFICATIONS

Power Supply Voltage	120V (60 Hz)	Individual Carton Dimensions	15.35"W x 11.22"D x 20.87"H 390 mm x 285 mm x 530 mm
Power Consumption	110 W	Individual Carton Weight	15.40 lbs. / 6.99 kgs
Entry Width	8.86 in. (225 mm)	Individual Carton UPC Code	849023020547
Auto-Feed Capacity	120 Sheets (Letter, A4 size / 80 g/m ² paper)	Master Carton Dimensions	15.35"W x 11.22"D x 20.87"H 390 mm x 285 mm x 530 mm
Manual Feed Capacity	5 Sheets (Letter, A4 size / 80 g/m ² paper)	Master Carton Weight	15.40 lbs. / 6.99 kgs
Speed	13.12 ft. (4 m) per minute	Master Carton Count	1
Basket Volume	6.6 gallon (25 L)	Master Carton UPC Code	50849023020542
Dimensions	14.17" x 10.04" x 20.87" 360 mm x 255 mm x 530 mm		
Weight	14.08 lbs. / 6.40 kgs		

1 Year Parts Warranty
3 Year Cutting Blade Warranty