

CH-400V Industrial "Climbing" Hard Hat — Vented

Key Features and Benefits:

- Ideal for at-height and scaffolding work, confined space applications, construction sites requiring chin straps and general all-around head protection
- Lightweight design is molded from high-quality ABS materials
- Includes a replaceable extra-absorbent sweatband
- · More comfortable than traditional hard hats
- Slotted adapters allow use with multiple Jackson- and Sellstrom-brand hard hat accessories including face shield adapters and earmuffs
- Dual rear slots allow use of optional red reflector for improved safety
- Meets ANSI Z89.1, Type 1, Class C











Product Number	Color	Suspension	Case Count
20920	White	6-pt. Rapid Dial	20
20921	Yellow	6-pt. Rapid Dial	20
20923	Orange	6-pt. Rapid Dial	20
20926	Hi-Vis Green	6-pt. Rapid Dial	20
20927	Black	6-pt. Rapid Dial	20



325 Corporate Drive Elgin, IL 60123 USA Toll Free Tel: 1-800-323-7402 Fax: 847-717-8419 email: orders.usa@surewerx.com

jacksonsafety.com



Replacement Parts and Accessories










Capmount H70 Ear Muff 20776, 20777, 20778 (Hard hat and ear muffs sold separately)



Face shield and ear muffs sold separately









Customize Your Hard Hat With Your Company Logo!

- · Scan the barcode with your device
- · Fill out the easy-to-use online form
- · A proof will be returned within 3 days









20937 (Hard hat sold separately)

