

## CH-300 Industrial "Climbing" Hard Hat — Non-Vented

## **Key Features and Benefits:**

- Ideal for at-height and scaffolding work, confined space applications, construction sites requiring chin straps, and general all-around head protection
- Lightweight design is molded from high-density polyethylene (HDPE)
- · Includes a replaceable extra-absorbent sweatband
- · More comfortable than traditional hard hats
- Slotted adapters allow use with multiple Jackson- and Sellstrom-brand hard hat accessories including face shield adapters and earmuffs
- Dual rear slots allow use of optional red reflector for improved safety
- Meets ANSI Z89.1, Type 1, Class C, G, E, and EN397 European Standards











Product Number	Color	Suspension	Case Count
20900	White	6-pt. Rapid Dial	20
20901	Yellow	6-pt. Rapid Dial	20
20903	Orange	6-pt. Rapid Dial	20
20906	Hi-Vis Green	6-pt. Rapid Dial	20
20907	Black	6-pt. Rapid Dial	20



email: orders.usa@surewerx.com jacksonsafety.com



## **Replacement Parts and Accessories**










Capmount H70 Ear Muff 20776, 20777, 20778 (Hard hat and ear muffs sold separately)



16797 Face shield and ear muffs sold separately







20933



## **Customize Your Hard Hat** With Your Company Logo!

- · Scan the barcode with your device
- · Fill out the easy-to-use online form
- · A proof will be returned within 3 days







20937 (Hard hat sold separately)

