

Blockhead[®] FG Premium Fiberglass Full Brim Hard Hat





Special fiberglass materials for high-heat applications

Unique carbon fiber design pattern ensures a stylish, modern, and cool look!

Available in vented and non-vented models

SPEED DIAL

ratcheting headgear

Premium 370 Speed Dial®

Comfortable 4-pt. headgear suspension Extra-wide brim protects the worker from elements such as sun and rain



Key Features and Benefits:

· Vented style reduces heat build-up when

working in direct sun, hot climates and

stylish ridgeline for unique identification
Features Jackson's 370 Speed Dial[®] ratcheting headgear — an industry best!
Non-vented styles meet ANSI Z89.1,

• Vented styles meet ANSI Z89.1 Class C

other high-heat applications found in

· Contoured dome shape with modern,

· Premium-style wide-brim design

steel mills and foundries

Class C, G, and E







Product Number	Color	Model	Suspension	Case Count
20600	Composite Wrap	Non-vented	4-pt. 370 Speed Dial	20
20620	Composite Wrap	Vented	4-pt. 370 Speed Dial	20



surewerx.com

325 Corporate Drive Elgin, IL 60123 USA

Toll Free Tel: 1-800-323-7402 Fax: 847-717-8419 email: orders.usa@surewerx.com jacksonsafety.com



Replacement Parts and Accessories



14496



14461



20630

Replacement Parts & Accessories	Description	Case Count
14496	AA-8 Windgard® Head Protection	12/Pack
14461	Full Brim Sun Shade Adapter	1
20630	Replacement Ratcheting Headgear	12
20231	Replaceable Sweatbands	20/Pack
20832	Optional Chin Strap	1/Pack





20832



Customize Your Hard Hat With Your Company Logo!

- Scan the barcode with your device
- Fill out the easy-to-use online form
- A proof will be returned within 3 days

325 Corporate Drive Elgin, IL 60123 USA Toll Free Tel: 1-800-323-7402 Fax: 847-717-8419 email: orders.usa@surewerx.com jacksonsafety.com



surewerx.com