

Project Name

Location

Prepared By



NUVO 60-127

2 LT - 11" FLUSH FIXTURE

Notes

[www] 02-27-2023 01:59:10

General

Status	Active
Finish	Matte Black
Style	Transitional
Number of Lamps	2
Height (in.)	4.88
Width (in.)	11.38
Indoor or Outdoor Fixture	Indoor

Specifications

Base	Medium
Bulb Type	Incandescent
Max Wattage	60W
Voltage	120V
Bulb Included	No
Glass Description	White
Weight (lb.)	3.45
Fixture Type	Flush Mount
Fixture Material	Steel

Compliance

Safety Listing	cULus
Location Rating	Damp
UL Application	Ceiling
Energy Star	No
CA T20 / T24 Rationale	T20 Exempt - Fixtures Not Regulated
California Status	Lawful for sale in California
Title 20 / 24 Status	Lawful for sale
California Prop 65	Lead
RoHS Compliant	Yes

Additional Information

Warranty	1 Year Limited - Fixtures
----------	---------------------------