

Project Name

Location

Prepared By



## NUVO 60-6117

HOPKINS 1LT OUTDOOR HANGING

### Notes

[www] 11-07-2022 01:45:33

### General

Status	Active
Collection	Hopkins
Finish	Matte Black
Style	Traditional
Number of Lamps	1
Height (in.)	12.67
Width (in.)	7.38
Indoor or Outdoor Fixture	Outdoor

### Specifications

Base	Medium
Bulb Type	Incandescent
Max Wattage	100W
Voltage	120V
Bulb Included	No
Glass Description	Clear Glass
Fabric Description	Glass
Weight (lb.)	3.15
Fixture Type	Hanging Lantern
Fixture Material	Die-Cast Aluminum / Glass

### Dimensions

Back Plate or Canopy Height (in.)	0.75
Back Plate or Canopy Diameter (in.)	4.75
Chain Length	48 in.

### Compliance

Safety Listing	cULus
Location Rating	Wet
Energy Star	No
ADA Compliant	No
NSF Approved	No
CA T20 / T24 Rationale	T20 Exempt - Fixtures Not Regulated
California Status	Lawful for sale in California
Title 20 / 24 Status	Lawful for sale
California Prop 65	Lead
RoHS Compliant	No
FCC Compliant	No

### Additional Information

Additional Information	Paint Coating; Waterproof
Warranty	1 Year Limited - Fixtures