

Project Name

Location

Prepared By



NUVO 60-7673

LINCOLN 1LT SEMI FL MATTE BLK

Notes

[www] 05-06-2023 01:09:30

General

| | |
|---------------------------|--------------|
| Status | Active |
| Collection | Lincoln |
| Finish | Matte Black |
| Style | Transitional |
| Number of Lamps | 1 |
| Height (in.) | 12.00 |
| Width (in.) | 11.00 |
| Indoor or Outdoor Fixture | Indoor |

Specifications

| | |
|-------------------|--------------|
| Base | Medium |
| Bulb Type | Incandescent |
| Max Wattage | 60W |
| Bulb Included | No |
| Glass Description | Clear Seeded |
| Weight (lb.) | 5.08 |
| Sloped Ceiling | No |
| Fixture Type | Semi Flush |
| Fixture Material | Steel |

Dimensions

| | |
|-------------------------------------|------|
| Back Plate or Canopy Height (in.) | 0.79 |
| Back Plate or Canopy Diameter (in.) | 4.92 |

Compliance

| | |
|------------------------|-------------------------------------|
| Safety Listing | cULus |
| Location Rating | Damp |
| CA T20 / T24 Rationale | T20 Exempt - Fixtures Not Regulated |
| California Status | Lawful for sale in California |
| Title 20 / 24 Status | Lawful for sale |
| California Prop 65 | Lead |

Additional Information

| | |
|----------|---------------------------|
| Warranty | 1 Year Limited - Fixtures |
|----------|---------------------------|