

Project Name

Location

Prepared By



NUVO 60-7674

LINCOLN 1LT MED PEND MATTE BLK

Notes

[www] 05-06-2023 01:09:30

General

Status	Active
Collection	Lincoln
Finish	Matte Black
Style	Transitional
Number of Lamps	1
Height (in.)	16.25
Width (in.)	11.00
Indoor or Outdoor Fixture	Indoor

Specifications

Base	Medium
Bulb Type	Incandescent
Max Wattage	60W
Bulb Included	No
Glass Description	Clear Seeded
Weight (lb.)	6.20
Sloped Ceiling	Yes
Fixture Type	Pendant
Fixture Material	Steel

Dimensions

Back Plate or Canopy Height (in.)	0.79
Back Plate or Canopy Diameter (in.)	4.92

Compliance

Safety Listing	cULus
Location Rating	Damp
CA T20 / T24 Rationale	T20 Exempt - Fixtures Not Regulated
California Status	Lawful for sale in California
Title 20 / 24 Status	Lawful for sale
California Prop 65	Lead

Additional Information

Warranty	1 Year Limited - Fixtures
----------	---------------------------