

Project Name

Location

Prepared By



## NUVO 60-7684

STARLIGHT 3LT SEMI FLUSH

**Notes**

[www] 05-06-2023 01:09:30

**General**

Status	Active
Collection	Starlight
Finish	Matte Black/Natural Brass
Style	Transitional
Number of Lamps	3
Height (in.)	10.75
Width (in.)	19.00
Indoor or Outdoor Fixture	Indoor

**Specifications**

Base	Medium
Bulb Type	Incandescent
Max Wattage	60W
Bulb Included	No
Glass Description	Clear Seeded
Weight (lb.)	4.05
Sloped Ceiling	No
Fixture Type	Semi Flush
Fixture Material	Steel

**Dimensions**

Back Plate or Canopy Height (in.)	0.79
Back Plate or Canopy Diameter (in.)	4.92

**Compliance**

Safety Listing	cULus
Location Rating	Damp
CA T20 / T24 Rationale	T20 Exempt - Fixtures Not Regulated
California Status	Lawful for sale in California
Title 20 / 24 Status	Lawful for sale
California Prop 65	Lead

**Additional Information**

Warranty	1 Year Limited - Fixtures
----------	---------------------------