SATCO" NUVO"

Project Name

Location

Prepared By



DESTIN 4L	T ISI AND	PFNDANT

Notes

[www] 03-06-2023 01:08:30

General	
Status	Active
Collection	Destin
Finish	Black / Silver Accents
Style	Contemporary
Number of Lamps	4
Height (in.)	7.625
Width (in.)	5.50
Length (in.)	38.00
Indoor or Outdoor Fixture	Indoor
Specifications	

Base	Medium
Bulb Type	Incandescent
Max Wattage	60W
Bulb Included	No
Glass Description	Clear Ribbed
Weight (lb.)	8.69
Sloped Ceiling	No
Fixture Type	Island Pendant
Fixture Material	Steel

Dimensions	
Back Plate or Canopy Length (in.)	4.53
Back Plate or Canopy Width (in.)	6.30
Back Plate or Canopy Height (in.)	0.98

Compliance	
Safety Listing	cULus
Location Rating	Damp
CA T20 / T24 Rationale	T20 Exempt - Fixtures Not Regulated
California Status	Lawful for sale in California
Title 20 / 24 Status	Lawful for sale
California Prop 65	Lead
Additional Information	

Warranty

1 Year Limited - Fixtures

For More Information Visit: <u>http://www.satco.com/</u>

