

Project Name

Location

Prepared By



NUVO 60-7821

AMADO 3 LIGHT SEMI FLUSH MOUNT

Notes

[www] 07-05-2023 01:10:03

General

Status	Active
Collection	Amado
Finish	Vintage Brass
Style	Transitional
Number of Lamps	3
Height (in.)	14.25
Width (in.)	14.00
Indoor or Outdoor Fixture	Indoor

Specifications

Base	Candelabra
Bulb Type	Incandescent
Max Wattage	60W
Bulb Included	No
Glass Description	Clear
Weight (lb.)	6.13
Fixture Shape	Bowl
Fixture Type	Semi Flush Mount
Fixture Material	Steel

Dimensions

Back Plate or Canopy Height (in.)	1.00
Back Plate or Canopy Diameter (in.)	7.00

Compliance

Safety Listing	cETLus - Listed
Location Rating	Dry
Energy Star	No
DLC Approved	No
California Prop 65	Lead

Additional Information

Warranty	1 Year Limited - Fixtures
----------	---------------------------