

Project Name

Location

Prepared By



NUVO 62-1108

12W LED TAPER BACK MONOPOINT

Notes

[www] 09-07-2020 02:17:44

General

Status	Active
Type	Monopoint
Wattage	12
Finish	White
Beam Angle	36
CCT (Kelvin)	3000
Temperature	Warm White

Specifications

CRI	90
Lumen Output	1020
Rated Hours	30000
Voltage	120V
Dimmable	Yes - Dimmable
Compatible Dimmers	Triac
Weight (lb.)	1.03

Dimensions

Height (in.)	4.50
Width (in.)	4.75
Length (in.)	4.75

Compliance

Safety Listing	cETLus
Location Rating	Dry
UL Application	Ceiling
Energy Star	No
CEC Status	Lawful for sale in California
CA Prop 65	Lead
RoHS Compliant	Yes

Additional Information

Warranty	3 Year Limited - Fixtures
----------	---------------------------