

Project Name

Location

Prepared By



## NUVO 62-1197

LED 6W LANDSCAPE FLOOD

### Notes

[www] 01-15-2024 02:40:00

### General

Status	Active
Fixture Type	Flood Light
Finish	Matte Black
Wattage	6W
Lumen Output	640L
CCT (Kelvin)	3000K
Temperature	Warm White
Indoor or Outdoor Fixture	Outdoor

### Specifications

Technology	LED
CRI	80
Voltage	120V
Beam Angle	60
Rated Hours	50000
Operating Temperature	-20C (-4F) to +40C (+104F)
Dimmable	Non-Dimmable
Photocell or Sensor	No Photocell
Lens Material	Glass
Weight (lb.)	0.62
Material	Die-cast Aluminum

### Dimensions

Height (in.)	3.25
Width (in.)	2.45
Length (in.)	5.5

### Compliance

Safety Listing	cULus - Listed
Location Rating	Wet
Energy Star	No
CA T20 / T24 Rationale	T20 Exempt - Fixtures Not Regulated
California Status	Lawful for sale in California
Title 20 / 24 Status	Lawful for sale
California Prop 65	Lead
RoHS Compliant	Yes
FCC Compliant	Yes
SDS Sheet	LED_Fixture

### Additional Information

Warranty	5 Year Limited - Fixtures
----------	---------------------------