

Project Name

Location

Prepared By



NUVO 62-1391

LED OVAL BULK HEAD

Notes

[www] 06-06-2022 10:07:59

General

Status	Active
Finish	Black
Wattage	18.5W
CCT (Kelvin)	3000K
Color Temperature	Warm White
Width (in.)	6.46
Height (in.)	11.03
Extension (in.)	5.05
Indoor or Outdoor Fixture	Outdoor

Specifications

Technology	LED
CRI	90
Lumen Output	1000L
Rated Hours	50000
Voltage	120V
Dimmable	Yes-Dimmable
Dimming Note	Dimming range from 100 to less than or equal to 20 percent depending on dimmer control
Glass Description	White
Weight (lb.)	2.57
Fixture Material	Die Cast Aluminum
Fixture Type	Bulk Head
Operating Temperature	-17C (-1.4F) to a maximum of +45C (+113F)

Compliance

Safety Listing	cETLus - Listed
Location Rating	Wet
Energy Star	Yes
ES Unique ID	ESID-2393483
CA T20 / T24 Rationale	California T24 2016 & 2019 JA8 Listed
California Status	Lawful for sale in California
Title 20 / 24 Status	California T24 Listed
California Prop 65	Lead
RoHS Compliant	Yes
FCC Compliant	Yes

Additional Information

Warranty	5 Year Limited - Fixtures
----------	---------------------------