

Project Name

Location

Prepared By



Notes

[www] 07-05-2023 01:10:03

General

Status	Active
Collection	Solano
Finish	Matte Black
Wattage	26W
Style	Contemporary
CCT (Kelvin)	3000K
Color Temperature	Warm White
Width (in.)	24.00
Height (in.)	4.25
Extension (in.)	4.25
Indoor or Outdoor Fixture	Indoor

Smart Product Info

IOT Enabled	No
-------------	----

Specifications

Technology	LED
CRI	90
Lumen Output	2080L
Rated Hours	30000
Voltage	120V
Dimmable	Yes_Dimmable
Weight (lb.)	2.90
Up/Down Installation	Up or Down
Fixture Material	Steel
Fixture Type	Vanity

Dimensions

Back Plate or Canopy Length (in.)	4.50
Back Plate or Canopy Width (in.)	0.25
Back Plate or Canopy Height (in.)	6.00

Compliance

Safety Listing	cETLus - Listed
Location Rating	Damp
Energy Star	No
DLC Approved	No
California Prop 65	Lead
SDS Sheet	LED_Fixture

Additional Information

Warranty	3 Year Limited - Fixtures
----------	---------------------------