

Project Name

Location

Prepared By



Notes

[www] 10-04-2021 00:36:20

General

Status	Active
Finish	Brushed Nickel
Wattage	12W
CCT (Kelvin)	3000
Color Temperature	Warm White
Length (in.)	8.00
Width (in.)	8.00
Height (in.)	3.50
Indoor or Outdoor Fixture	Indoor

Specifications

Technology	LED
CRI	90
Lumen Output	1000L
Rated Hours	50000
Voltage	120V
Dimmable	Non-Dimmable
Glass Description	Frosted
Fixture Material	Steel
Fixture Type	Flush Mount

Compliance

Safety Listing	cETLus
California Status	Lawful for sale
California Prop 65	Lead
RoHS Compliant	Yes
FCC Compliant	Yes

Additional Information

Warranty	3 Year Limited - Fixtures
----------	---------------------------