

Project Name

Location

Prepared By



NUVO 62-1582

4" LED SURFACE MOUNT/BR NICKEL

Notes

[www] 04-05-2020 05:00:00

General

Status	Active
Fixture Type	Surface Mount
Finish	Brushed Nickel
Wattage	9W
Lumen Output	680L-720L
CCT (Kelvin)	3000K/4000K/5000K
Indoor or Outdoor Fixture	Indoor

Specifications

Technology	LED
Color Temperature	Warm to Cool White
CRI	90
Voltage	120V
Beam Angle	90
Rated Hours	50000
Operating Temperature	-20C (-4F) to a maximum of +40C (+104F)
Dimmable	Yes-Dimmable
Dimming Note	Dimming range from 100 to less than or equal to 20 percent depending on dimmer control
Lens Material	Polycarbonate (PC)
Weight (lb.)	0.31
Material	Aluminum

Dimensions

Height (in.)	1.31
Width (in.)	4.67

Compliance

Safety Listing	cETLus
Location Rating	Wet
Energy Star	Yes
ES Unique ID	ESID-2389611
CA T20 / T24 Rationale	California T24 2016 & 2019 JA8 Compliant
California Status	Lawful for sale in California
Title 20 / 24 Status	California T24 Compliant
California Prop 65	Lead
RoHS Compliant	Yes
FCC Compliant	Yes

Additional Information

Additional Information	Lens Aperture is 2.81
Warranty	5 Year Limited - Fixtures