

Project Name

Location

Prepared By



NUVO 62-1583

4" LED SURFACE MOUNT/BRONZE

Notes

[www] 04-05-2020 05:00:00

General

| | |
|---------------------------|-------------------|
| Status | Active |
| Fixture Type | Surface Mount |
| Finish | Bronze |
| Wattage | 9W |
| Lumen Output | 680L-720L |
| CCT (Kelvin) | 3000K/4000K/5000K |
| Indoor or Outdoor Fixture | Indoor |

Specifications

| | |
|-----------------------|--|
| Technology | LED |
| Color Temperature | Warm to Cool White |
| CRI | 90 |
| Voltage | 120V |
| Beam Angle | 90 |
| Rated Hours | 50000 |
| Operating Temperature | -20C (-4F) to a maximum of +40C (+104F) |
| Dimmable | Yes-Dimmable |
| Dimming Note | Dimming range from 100 to less than or equal to 20 percent depending on dimmer control |
| Lens Material | Polycarbonate (PC) |
| Weight (lb.) | 0.31 |
| Material | Aluminum |

Dimensions

| | |
|--------------|------|
| Height (in.) | 1.31 |
| Width (in.) | 4.67 |

Compliance

| | |
|------------------------|--|
| Safety Listing | cETLus |
| Location Rating | Wet |
| Energy Star | Yes |
| ES Unique ID | ESID-2389608 |
| CA T20 / T24 Rationale | California T24 2016 & 2019 JA8 Compliant |
| California Status | Lawful for sale in California |
| Title 20 / 24 Status | California T24 Compliant |
| California Prop 65 | Lead |
| RoHS Compliant | Yes |
| FCC Compliant | Yes |

Additional Information

| | |
|------------------------|---------------------------|
| Additional Information | Lens Aperture is 2.81 |
| Warranty | 5 Year Limited - Fixtures |