

Project Name

Location

Prepared By



NUVO 62-1632

LED GLAMOUR 49" BN VANITY

Notes

[www] 06-27-2021 00:19:09

General

Status	Active
Collection	Glamour
Finish	Brushed Nickel
Wattage	52W
CCT (Kelvin)	3000K/4000K/5000K
Color Temperature	Warm to Cool White
Width (in.)	49.00
Height (in.)	5.50
Extension (in.)	3.00
Indoor or Outdoor Fixture	Indoor

Specifications

Technology	LED
CRI	90
Lumen Output	4160L/4680L/4420L
Rated Hours	50000
Voltage	120V
Dimmable	Yes-Dimmable
Weight (lb.)	6.95
Up/Down Installation	Up/Down
Fixture Material	Steel
Fixture Type	Vanity

Dimensions

Back Plate or Canopy Length (in.)	49.00
Back Plate or Canopy Width (in.)	5.50

Compliance

Safety Listing	cETLus
Location Rating	Damp
UL Application	Wall - Up or Down
Energy Star	Pending
ADA Compliant	Yes
California Status	Lawful for sale
California Prop 65	Lead
RoHS Compliant	Yes
FCC Compliant	Yes

Additional Information

Warranty	3 Year Limited - Fixtures
----------	---------------------------