

Project Name

Location

Prepared By



NUVO 62-1653

SUPREME 10W LED SM WALL LANT

Notes

[www] 11-29-2021 04:01:39

General

Status	Active
Collection	Supreme
Finish	Matte Black
Wattage	10W
Style	Modern
CCT (Kelvin)	3000K
Color Temperature	Warm White
Width (in.)	4.875
Height (in.)	11.000
Extension (in.)	4.250
Indoor or Outdoor Fixture	Outdoor

Specifications

Technology	LED
CRI	90+
Lumen Output	900L
Rated Hours	30000
Dimmable	Yes-Dimmable
Glass Description	Clear
Weight (lb.)	2.36
Up/Down Installation	Down Only
Fixture Material	Iron / Glass
Fixture Type	Wall Lantern
Operating Temperature	-20C (-4F) to a maximum of +40C (+104F)

Dimensions

Back Plate or Canopy Length (in.)	4.900
Back Plate or Canopy Width (in.)	4.900
Back Plate or Canopy Height (in.)	0.790

Compliance

Safety Listing	cETLus
Location Rating	Wet
Energy Star	No
ADA Compliant	No
California Status	California T24 Compliant
California Prop 65	Lead
RoHS Compliant	No
FCC Compliant	No

Additional Information

Warranty	3 Year Limited - Fixtures
----------	---------------------------