

Project Name

Location

Prepared By



Notes

[www] 06-30-2020 02:05:41

General

Status	Active
Finish	Brushed Nickel
Wattage	16W
CCT (Kelvin)	3000K/4000K/5000K
Color Temperature	Warm to Cool White
Width (in.)	9.49
Height (in.)	1.28
Indoor or Outdoor Fixture	Indoor

Specifications

Technology	LED
CRI	90
Lumen Output	1120L-1220L
Rated Hours	50000
Voltage	120V
Dimmable	Yes-Dimmable
Dimming Note	Dimming range from 100 to less than or equal to 20 percent depending on dimmer control
Fabric Description	Frosted
Weight (lb.)	1.22
Sloped Ceiling	Yes
Fixture Shape	Round
Fixture Material	Steel
Fixture Type	Disk Light
Operating Temperature	-35C (-31F) to a maximum of +50C (+122F)

Compliance

Safety Listing	cETLus
Location Rating	Wet
Energy Star	Pending
CA T20 / T24 Rationale	T20 Exempt - Fixtures Not Regulated
California Status	Lawful for sale in California
Title 20 / 24 Status	Lawful for sale
California Prop 65	Lead
NEC Compliance	Clothes Closet Certified - Reg: 410.16 (A)(3) and 410.16 (C)(5)
RoHS Compliant	Yes
FCC Compliant	Yes
SDS Sheet	LED_Fixture

Additional Information

Specification Note	3000K = 1120L; 4000K = 1220L; 5000K = 1160L
Warranty	5 Year Limited - Fixtures