SATCO NUVO

Project Name

Location

Prepared By



NUVO 62-1711

11W LED 7" RND BLACK

Notes

General	
Status	Active
Fixture Type	Flush Mount
Finish	Black
Wattage	11W
Lumen Output	900L-950L
CCT (Kelvin)	2700K/3000K/3500K/4000K/5000K
Indoor or Outdoor Fixture	Indoor

LED

Specifications

NEC Compliance

FCC Compliant

Flicker Free

SDS Sheet

Technology

Color Temperature	Warm to Cool White
CRI	90
Voltage	120V
Beam Angle	100
Rated Hours	50000
Operating Temperature	-20C (-4F) to +40C (+104F)
Dimmable	Yes-Dimmable
Dimming Note	120V only
Lens Material	Poly methyl methacrylate (PMMA)
Surge Protection	Built-in surge protection - 2.5KV
Weight (lb.)	0.88
Material	Die Cast Aluminum
Dimensions	
Height (in.)	0.67
Width (in.)	7.00
Compliance	
Safety Listing	cETLus
Location Rating	Wet
Energy Star	Yes
ES Unique ID	ESID-2402974
CA T20 / T24 Rationale	California T24 2016 - 2022 JA8 Listed
California Status	Lawful for sale in California
Title 20 / 24 Status	California T24 Listed
California Prop 65	Lead
RoHS Compliant	Yes

Additional Information	
Additional Information	UGR - 26.97; SDCM - 464; Hi pot - DC-1550V; Edge-lit - Yes
Specification Note	Overall height of fixture and driver: 1.59"
Installation Notes	Surface mount; Compatible with 3"&4" J-box and pancake J-box with additional accessory
Warranty	5 Year Limited - Fixtures

Yes

No

LED_Fixture

Clothes Closet Certified - Reg:

410.16 (A)(3) and 410.16 (C)(5)







