

Project Name

Location

Prepared By



NUVO 62-1751

LED 5" ROUND SURFACE MOUNT 11W

Notes

[www] 05-15-2023 01:50:04

General

Status	Active
Finish	White
Wattage	11W
Style	Contemporary
CCT (Kelvin)	3000K
Color Temperature	Soft White
Width (in.)	5.31
Height (in.)	0.71
Indoor or Outdoor Fixture	Indoor

Smart Product Info

IOT Enabled	No
-------------	----

Specifications

Technology	LED
CRI	90+
Lumen Output	600L
Rated Hours	50000
Voltage	120V
Dimmable	Yes-Dimmable
Weight (lb.)	0.82
Fixture Shape	Round
Fixture Material	Polycarbonate (PC)
Fixture Type	Disk Light
Operating Temperature	-20C (-4F) to +40C (+104F)

Compliance

Safety Listing	cETLus
Location Rating	Wet
Energy Star	Yes
ES Unique ID	ESID-2404051
CA T20 / T24 Rationale	California T24 2016 - 2022 JA8 Listed
California Status	Lawful for sale in California
Title 20 / 24 Status	California T24 Listed
California Prop 65	Lead
FCC Compliant	Yes
SDS Sheet	LED_Fixture

Additional Information

Includes	E26 adaptor
Warranty	5 Year Limited - Fixtures