

Project Name

Location

Prepared By



Notes

[www] 05-15-2023 01:50:04

General

Status	Active
Fixture Type	Surface mount
Finish	White
Wattage	24W
Lumen Output	1650L-1900L
CCT (Kelvin)	2700K/3000K/3500K/4000K/5000K
Indoor or Outdoor Fixture	Indoor

Specifications

Technology	LED
Color Temperature	Warm to Cool White
CRI	90
Voltage	120V/277V
Rated Hours	50000
Operating Temperature	-20C (-4F) to +40C (+104F)
Dimmable	Yes-Dimmable
Dimming Note	120V only
Lens Material	Poly methyl methacrylate (PMMA)
Surge Protection	Built-in surge protection - 2.5KV
Weight (lb.)	4.92
Material	Metal

Dimensions

Height (in.)	1.06
Width (in.)	23.70
Length (in.)	11.83

Compliance

Safety Listing	cETLus - Listed
Location Rating	Damp
Energy Star	Yes
ES Unique ID	ESID-2405315
CA T20 / T24 Rationale	California T24 2016 - 2022 JA8 Listed
California Status	Lawful for sale in California
Title 20 / 24 Status	California T24 Listed
California Prop 65	Lead
RoHS Compliant	Yes
FCC Compliant	Yes
Flicker Free	No
SDS Sheet	LED_Fixture

Additional Information

Additional Information	UGR - 19.7; Hi pot - DC-1550V; Edge-lit - Yes
Installation Notes	Compatible with 3" & 4" J-box and pancake J-box
Warranty	5 Year Limited - Fixtures