

Project Name

Location

Prepared By

NUVO 63-503

UNDER CAB LED SCCT 22" - WH

Notes

[www] 08-02-2021 00:20:20

General

Status	Active
Finish	White
Wattage	13W
CCT (Kelvin)	3000K/4000K/5000K
Color Temperature	Warm to Cool White
Length (in.)	22
Width (in.)	3.5
Height (in.)	1
Indoor or Outdoor Fixture	Indoor

Specifications

Technology	LED
CRI	90+
Lumen Output	858L-954L
Rated Hours	40000
Voltage	120V
Dimmable	Yes-Dimmable
Weight (lb.)	1.28
Sloped Ceiling	No
Fixture Shape	Rectangle
Fixture Material	Aluminum and Polycarbonate (PC)
Fixture Type	Under Cabinet
Max. Connectable Units	36
Operating Temperature	-20C (-4F) to a maximum of +40C (+104F)

Compliance

Safety Listing	cETLus
Location Rating	Dry
Energy Star	Pending
California Status	California T24 Compliant
California Prop 65	Lead
RoHS Compliant	Yes
FCC Compliant	Yes

Additional Information

Warranty	5 Year Limited - Fixtures
----------	---------------------------