

Project Name

Location

Prepared By



NUVO 63-700

UNDER CAB LIGHT BAR LED 18"

Notes

[www] 06-30-2021 01:55:03

General

Status	Active
Finish	White
Wattage	10W
CCT (Kelvin)	3000
Color Temperature	Warm White
Length (in.)	18
Width (in.)	2.6
Height (in.)	0.75
Indoor or Outdoor Fixture	Indoor

Specifications

Technology	LED
CRI	80
Lumen Output	860L
Rated Hours	50000
Voltage	120V
Dimmable	Non-Dimmable
Weight (lb.)	0.67
Sloped Ceiling	No
Fixture Material	Aluminum and Polycarbonate (PC)
Fixture Type	Under Cabinet
Operating Temperature	-20C (-4F) to a maximum of +45C (+113F)

Dimensions

Wire Length	59 in.
-------------	--------

Compliance

Safety Listing	cETLus
Location Rating	Damp
Energy Star	No
California Status	California T24 Compliant
California Prop 65	Lead
RoHS Compliant	Yes
FCC Compliant	Yes

Additional Information

Includes	Wood Screws and 2 White Foam Adhesive Mounting Strips
Warranty	5 Year Limited