

Project Name

Location

Prepared By



NUVO 64-100

TAPE/RGB/IP20/PLUG/16'

Notes

[www] 06-07-2023 01:05:15

General

Status	Active
Fixture Type	Tape Light
Finish	White
Wattage	14W
Lumen Output	580L
IP Rating	IP20
Indoor or Outdoor Fixture	Indoor

Smart Product Info

IOT Enabled	No
-------------	----

Specifications

Technology	LED
Color Temperature	RGB
CRI	80+
Voltage	12V
Rated Hours	50000
Operating Temperature	-20C (-4F) to +40C (+104F)
Dimmable	Yes-Dimmable
Dimming Note	Dimmable with Remote
Weight (lb.)	1.01
Material	Plastic

Dimensions

Width (in.)	0.47
Length (in.)	196.85

Compliance

Safety Listing	cETLus - Listed
Location Rating	Dry
Energy Star	No
DLC Approved	No
CA T20 / T24 Rationale	T20 Exempt - Fixtures Not Regulated
California Status	Lawful for sale in California
Title 20 / 24 Status	Lawful for sale
California Prop 65	Lead
RoHS Compliant	Yes
FCC Compliant	Yes
SDS Sheet	LED_Fixture

Additional Information

Additional Information	Driver Wattage is 24W; Driver Voltage is 120V
Specification Note	Cuttable: Yes; Distance between cuts: 3.94" (100mm); Standard Brightness
Installation Notes	1 reel of 16 feet (5M); 9 Foot (3M) plug in tape pre-installed on back for quick installation
Includes	Kit includes: Plug-in Driver; Receiver; IR Remote; 1-5M Reel
Warranty	1 Year Limited - Fixtures

