

Project Name

Location

Prepared By



NUVO 64-121

TAPE/RGBTW/IP20/JBOX/SF/16'

Notes

[www] 06-07-2023 01:05:15

General

Status	Active
Fixture Type	Tape Light
Finish	White
Wattage	14W
Lumen Output	1120L
IP Rating	IP20
Indoor or Outdoor Fixture	Indoor

Smart Product Info

IOT Enabled	Yes
Voice Assistants Supported	Google Home; Alexa; Siri; SmartThings

Specifications

Technology	LED
Color Temperature	RGB and Tunable White
CRI	80+
Voltage	24V
Rated Hours	50000
Operating Temperature	-20C (-4F) to +40C (+104F)
Dimmable	Yes-Dimmable
Dimming Note	Only with Starfish App or Remote Control
Weight (lb.)	3.3
Material	Plastic

Dimensions

Width (in.)	0.47
Length (in.)	196.85

Compliance

Safety Listing	cETLus - Listed
Location Rating	Dry
Energy Star	No
DLC Approved	No
CA T20 / T24 Rationale	T20 Exempt - Fixtures Not Regulated
California Status	Lawful for sale in California
Title 20 / 24 Status	Lawful for sale
California Prop 65	Lead
RoHS Compliant	Yes
FCC Compliant	Yes
SDS Sheet	LED_Fixture

Additional Information

Additional Information	Driver Wattage is 30W; Driver Voltage is 120V-277V
Specification Note	Cutable: Yes; Distance between cuts: 6.56" (166.67 mm); Standard Brightness; Sync to Music
Installation Notes	1 reel of 16 feet (5M); 9 Foot (3M) plug in tape pre-installed on back for quick installation
Includes	Kit includes: Driver/Junction Box; Controller/Receiver; IR Remote; 1-

