SATCO NUVO

Project Name

Location

Prepared By



NUVO 64-132

TAPE/RGBTW-HO/IP20/PLUG/SF/64'

Notes

General	
Status	Active
Fixture Type	Tape Light
Finish	White
Wattage	68W
Lumen Output	6300L
IP Rating	IP20
Indoor or Outdoor Fixture	Indoor
Smart Product Info	
IOT Enabled	Yes
Voice Assistants Supported	Google Home; Alexa; Siri; SmartThings
Specifications	
Technology	LED
Color Temperature	RGB and Tunable White
CRI	80+
Voltage	24V
Rated Hours	50000
Operating Temperature	-20C (-4F) to +40C (+104F)
Dimmable	Yes-Dimmable
Dimming Note	Only with Starfish App or Remote Control
Weight (lb.)	2.42
Material	Plastic
Dimensions	
Width (in.)	0.47
Length (in.)	787.44
Compliance	
Safety Listing	cETLus - Listed
Location Rating	Dry
Energy Star	No
DLC Approved	No
CA T20 / T24 Rationale	T20 Exempt - Fixtures Not Regulated
California Status	Lawful for sale in California
Title 20 / 24 Status	Lawful for sale
California Prop 65	Lead
RoHS Compliant	Yes
FCC Compliant	Yes
SDS Sheet	
	LED_Fixture
Additional Information	LED_Fixture
	Driver Wattage is 72W; Driver Voltage is 120V
Additional Information	Driver Wattage is 72W; Driver Voltage is 120V Cuttable: Yes; Distance between cuts: 4.92" (125 mm); High Brightness; Sync to Music
Additional Information Additional Information	Driver Wattage is 72W; Driver Voltage is 120V Cuttable: Yes; Distance between cuts: 4.92" (125 mm); High

Kit includes: Plug-in Driver;

Includes	Controller/Receiver; IR Remote; 2-10M Reels
Warranty	1 Year Limited - Fixtures

Copyright 2020 Satco Products, Inc. All Rights Reserved

For More Information Visit: http://www.satco.com/







