## **SATCO' NUVO**

Project Name

Location

Prepared By



## NUVO 64-140

TAPE/RGBTW-HO/IP65/PLUG/SF/16

Notes

General Status Active Fixture Type Tape Light Finish White Wattage 18W Lumen Output 1920L IP Rating IP65 Indoor or Outdoor Fixture Indoor; Outdoor Smart Product Info IOT Enabled Yes Google Home; Alexa; Siri; Voice Assistants Supported SmartThings Specifications LED Technology RGB and Tunable White Color Temperature 80+ CRI 24V Voltage 50000 Rated Hours -20C (-4F) to +40C (+104F) **Operating Temperature** Dimmable Yes-Dimmable Only with Starfish App or Remote **Dimming Note** Control Weight (lb.) 2.2 Plastic Material Dimensions Width (in.) 0.55 Length (in.) 196.85 Compliance Safety Listing cETLus - Listed Location Rating Wet Energy Star No **DLC Approved** No T20 Exempt - Fixtures Not CA T20 / T24 Rationale Regulated California Status Lawful for sale in California Title 20 / 24 Status Lawful for sale California Prop 65 Lead **RoHS** Compliant Yes FCC Compliant Yes SDS Sheet LED Fixture Additional Information Driver Wattage is 24W; Driver Additional Information Voltage is 120V Cuttable: No; Outdoor tape is not recommended to be cut as IP65 rating and warranty become Specification Note invalidated; High Brightness; Sync to Music 1 reel of 16 feet (5M); Mounting Installation Notes Clips for outdoor installation

Kit includes: Outdoor Rated Plug-

Includes

Warranty

in Driver; Receiver; RF Remote; 20 Mounting Clips; 1-5M Reel

1 Year Limited - Fixtures

Copyright 2020 Satco Products, Inc. All Rights Reserved For More Information Visit: <u>http://www.satco.com/</u>

