

Project Name

Location

Prepared By



Notes

[www] 06-07-2023 01:05:15

General

Status	Active
Fixture Type	Tape Light
Finish	White
Wattage	68W
Lumen Output	6300L
IP Rating	IP65
Indoor or Outdoor Fixture	Indoor; Outdoor

Smart Product Info

IOT Enabled	Yes
Voice Assistants Supported	Google Home; Alexa; Siri; SmartThings

Specifications

Technology	LED
Color Temperature	RGB and Tunable White
CRI	80+
Voltage	24V
Rated Hours	50000
Operating Temperature	-20C (-4F) to +40C (+104F)
Dimmable	Yes-Dimmable
Dimming Note	Only with Starfish App or Remote Control
Weight (lb.)	9.24
Material	Plastic

Dimensions

Width (in.)	0.55
Length (in.)	787.44

Compliance

Safety Listing	cETLus - Listed
Location Rating	Wet
Energy Star	No
DLC Approved	No
CA T20 / T24 Rationale	T20 Exempt - Fixtures Not Regulated
California Status	Lawful for sale in California
Title 20 / 24 Status	Lawful for sale
California Prop 65	Lead
RoHS Compliant	Yes
FCC Compliant	Yes
SDS Sheet	LED_Fixture

Additional Information

Additional Information	Driver Wattage is 80W; Driver Voltage is 120V-277V
Specification Note	Cuttable: No; Outdoor tape is not recommended to be cut as IP65 rating and warranty become invalidated; High Brightness; Sync to Music
Installation Notes	2 reels of 32 feet (10M) to make 64 feet (20M) total; Mounting Clips for outdoor installation

Includes	Kit includes: Outdoor Rated Driver/Junction Box; Receiver; RF Remote; 80 Mounting Clips; 2-10M Reels
Warranty	1 Year Limited - Fixtures

Copyright 2020 Satco Products, Inc.
All Rights Reserved

For More Information Visit:
<http://www.satco.com/>

