

Project Name

Location

Prepared By



## NUVO 65-538R1

LED 50W MEDIUM FLOOD LIGHT

### Notes

[www] 10-24-2020 09:32:00

### General

Status	Active
Finish	Bronze
Wattage	50W
Lumen Output	6650L
CCT (Kelvin)	4000K
Temperature	Cool White
IP Rating	IP65
Indoor or Outdoor Fixture	Outdoor

### Specifications

Technology	LED
CRI	80+
Voltage	120V-277V
Beam Angle	110x110
Rated Hours	50000
Operating Temperature	-30C (-22F) to +45C (+113F)
Dimmable	Yes-Dimmable
Dimming Note	0-10V Dimming
Surge Protection	Built-in surge protection - 2KV
Weight (lb.)	3.62

### Dimensions

Height (in.)	1.93
Width (in.)	8.50
Length (in.)	9.57

### Compliance

Safety Listing	cULus
Location Rating	Wet
Energy Star	No
DLC Approved	Yes
DLC ID	S-S6IGZ8
IC Rated	Yes
CA T20 / T24 Rationale	T20 Exempt - Fixtures Not Regulated
California Status	Lawful for sale in California
Title 20 / 24 Status	Lawful for sale
California Prop 65	Lead
RoHS Compliant	Yes
FCC Compliant	Yes
SDS Sheet	LED_Fixture

### Additional Information

Additional Information	1/2" Thread knuckle mount
Warranty	5 Year Limited - Fixtures