

Project Name

Location

Prepared By



NUVO 65-620R1

150W LED FLOOD LIGHT

Notes

[www] 06-22-2022 00:35:11

General

Status	Active
Fixture Type	Flood Light
Finish	Bronze
Wattage	150W
Lumen Output	20250L
CCT (Kelvin)	5000K
Temperature	Natural Light
IP Rating	IP65
Indoor or Outdoor Fixture	Outdoor

Specifications

Technology	LED
CRI	80+
Voltage	120V-347V
Beam Angle	150
Rated Hours	50000
Operating Temperature	-40C (-40F) to +50C (+122F)
Dimmable	Yes-Dimmable
Dimming Note	1-10V Dimming Only
Lens Material	Polycarbonate (PC)
Surge Protection	Built-in surge protection - 6KV
Weight (lb.)	15.65
Material	Aluminum Alloy

Dimensions

Height (in.)	2.63
Width (in.)	9.44
Length (in.)	13.19

Compliance

Safety Listing	cULus - Listed; cULus - Certified
Location Rating	Wet
Energy Star	No
DLC Approved	Yes
DLC ID	S-PYBT47
IC Rated	Yes
California Prop 65	Lead
RoHS Compliant	Yes
FCC Compliant	Yes
SDS Sheet	LED_Fixture

Additional Information

Specification Note	Add on photocell, sku 86-212, is only rated for 120-277 Volt
Warranty	5 Year Limited - Fixtures