

Project Name

Location

Prepared By



NUVO 65-632R1

100W LED CANOPY W/ SENSOR PORT

Notes

[www] 11-20-2023 01:02:45

General

Status	Active
Fixture Type	Canopy
Finish	Bronze
Wattage	100W
Lumen Output	14298L/15322/14943L
CCT (Kelvin)	3000K/4000K/5000K
IP Rating	IP65
Indoor or Outdoor Fixture	Outdoor

Specifications

Technology	LED
Color Temperature	Warm to Cool White
CRI	80
Voltage	120V-277V
Beam Angle	150
Rated Hours	50000
Operating Temperature	-40C (-40F) to +45C (+113F)
Dimmable	Yes-Dimmable
Dimming Note	0-10V Dimming
Photocell or Sensor	Optional Add-On
Lens Material	Polycarbonate (PC)
Surge Protection	Built-in surge protection - 6KV
Weight (lb.)	6.56
Material	Die-cast Aluminum

Dimensions

Height (in.)	3.15
Width (in.)	11.02

Compliance

Safety Listing	cULus - Listed
Location Rating	Wet
Energy Star	No
DLC Approved	Yes
DLC ID	S-ZW3LNP
B.U.G. Rating	B3-U3-G2
CA T20 / T24 Rationale	T20 Exempt - Fixtures Not Regulated
California Status	Lawful for sale in California
Title 20 / 24 Status	Lawful for sale
California Prop 65	Lead
RoHS Compliant	Yes
FCC Compliant	Yes
SDS Sheet	LED_Fixture

Additional Information

Specification Note	UV Stabilized Powder Coated Finish
Warranty	5 Year Limited - Fixtures

