

Project Name

Location

Prepared By



Notes

[www] 06-27-2022 03:48:17

General

Status	Active
Fixture Type	Linear Hi-Bay
Finish	White
Wattage	165W
Lumen Output	22816L
CCT (Kelvin)	5000K
IP Rating	IP40
Indoor or Outdoor Fixture	Indoor

Specifications

Technology	LED
Color Temperature	Natural Light
CRI	80+
Voltage	120V-277V
Beam Angle	100
Rated Hours	50000
Operating Temperature	-40C (-40F) to +50C (+122F)
Dimmable	Yes-Dimmable
Dimming Note	0-10V Dimming Only
Photocell or Sensor	Has PIR Sensor
Lens Material	Polycarbonate (PC)
Weight (lb.)	9.04
Material	Aluminum Alloy

Dimensions

Height (in.)	1.88
Width (in.)	12.00
Length (in.)	26.00

Compliance

Safety Listing	cUL - Listed
Location Rating	Damp
Energy Star	No
DLC Approved	Yes
DLC ID	S-E2HV7D
IC Rated	Yes
CA T20 / T24 Rationale	T20 Exempt - Fixtures Not Regulated
California Status	Lawful for sale in California
Title 20 / 24 Status	Lawful for sale
California Prop 65	Lead
RoHS Compliant	Yes
FCC Compliant	Yes
SDS Sheet	LED_Fixture

Additional Information

Warranty	5 Year Limited - Fixtures
----------	---------------------------