

Project Name

Location

Prepared By



NUVO 65-771R2

LED UFO HIGHBAY CCT & WATT ADJ

Notes

[www] 11-27-2023 00:55:51

General

Status	Active
Substitute	65-771R3
Fixture Type	UFO Hi-Bay
Finish	Black
Wattage	150W/175W/200W
Lumen Output	22200L-28800L
CCT (Kelvin)	3000K/4000K/5000K
IP Rating	IP65
Indoor or Outdoor Fixture	Indoor

Specifications

Technology	LED
Color Temperature	Warm White to Natural Light
CRI	80
Voltage	120V-277V
Beam Angle	90
Rated Hours	50000
Operating Temperature	-40C (-40F) to +50C (+122F)
Dimmable	Yes-Dimmable
Dimming Note	0-10V Dimming Only
Photocell or Sensor	Optional Add-On
Lens Material	Polycarbonate (PC)
Surge Protection	Built-in surge protection - 6KV
Weight (lb.)	6.42
Material	Die-cast Aluminum

Dimensions

Height (in.)	7.3
Width (in.)	13.4

Compliance

Safety Listing	cULus - Listed
Location Rating	Wet
Energy Star	No
DLC Approved	Yes
DLC ID	S-KCEODI
NSF Approved	Yes
CA T20 / T24 Rationale	T20 Exempt - Fixtures Not Regulated
California Status	Lawful for sale in California
Title 20 / 24 Status	Lawful for sale
California Prop 65	Lead
RoHS Compliant	Yes
FCC Compliant	Yes
SDS Sheet	LED_Fixture

Additional Information

Specification Note	Input Current at 120V: 1.69A
Installation Notes	Mounting Height: Up to 30 feet
Includes	Locking Hanging Hook; 6 Foot Whip
Warranty	5 Year Limited - Fixtures

