

Project Name

Location

Prepared By



NUVO 65-791

LED UFO HIGHBAY 100W/4000K

Notes

[www] 03-22-2021 04:50:54

General

Status	Active
Fixture Type	UFO Hi-Bay
Finish	White
Wattage	100
Lumen Output	14000
CCT (Kelvin)	4000
IP Rating	IP65

Specifications

Technology	LED
Color Temperature	Cool White
CRI	80
Voltage	120V-277V
Beam Angle	90
Rated Hours	50000
Operating Temperature	-40C (-40F) to a maximum of 45C (113F)
Dimmable	0-10V Dimming Only
Lens Material	Polycarbonate
Surge Protection	Built-in surge protection - 4KV
Weight (lb.)	6.58

Compliance

Safety Listing	cULus
Location Rating	Wet
California Prop 65	Lead
RoHS Compliant	Yes
FCC Compliant	Yes

Additional Information

Warranty	5 Year Limited - Fixtures
----------	---------------------------