

Project Name

Location

Prepared By



NUVO 65-793

LED UFO HIGHBAY 150W/4000K

Notes

[www] 03-15-2021 00:27:50

General

Status	Active
Fixture Type	UFO Hi-Bay
Finish	White
Wattage	150
Lumen Output	20850
CCT (Kelvin)	4000
IP Rating	IP65

Specifications

Technology	LED
Color Temperature	Cool White
CRI	80
Voltage	120V-277V
Beam Angle	90
Rated Hours	50000
Operating Temperature	-40C (-40F) to a maximum of 45C (113F)
Dimmable	0-10V Dimming Only
Surge Protection	Built-in surge protection - 4KV

Compliance

Safety Listing	cULus
California Prop 65	Lead
RoHS Compliant	Yes
FCC Compliant	Yes

Additional Information

Warranty	5 Year Limited - Fixtures
----------	---------------------------