

Project Name

Location

Prepared By



## NUVO 65-801R2

LED UFO HIGHBAY 100W/4000K

### Notes

[www] 11-20-2023 01:02:45

### General

|                           |            |
|---------------------------|------------|
| Status                    | Active     |
| Fixture Type              | UFO Hi-Bay |
| Finish                    | Black      |
| Wattage                   | 100W       |
| Lumen Output              | 14100L     |
| CCT (Kelvin)              | 4000K      |
| IP Rating                 | IP65       |
| Indoor or Outdoor Fixture | Indoor     |

### Specifications

|                       |                                 |
|-----------------------|---------------------------------|
| Technology            | LED                             |
| Color Temperature     | Cool White                      |
| CRI                   | 80                              |
| Voltage               | 277V-480V                       |
| Beam Angle            | 90                              |
| Rated Hours           | 50000                           |
| Operating Temperature | -40C (-40F) to +45C (+113F)     |
| Dimmable              | Yes-Dimmable                    |
| Dimming Note          | 0-10V Dimming Only              |
| Photocell or Sensor   | Optional Add-On                 |
| Lens Material         | Polycarbonate (PC)              |
| Surge Protection      | Built-in surge protection - 6KV |
| Weight (lb.)          | 6.58                            |
| Material              | Die-cast Aluminum               |

### Dimensions

|              |       |
|--------------|-------|
| Height (in.) | 8.11  |
| Width (in.)  | 11.02 |

### Compliance

|                        |                                     |
|------------------------|-------------------------------------|
| Safety Listing         | cULus - Listed                      |
| Location Rating        | Wet                                 |
| Energy Star            | No                                  |
| DLC Approved           | Yes                                 |
| DLC ID                 | S-LHQ20Y                            |
| NSF Approved           | Yes                                 |
| CA T20 / T24 Rationale | T20 Exempt - Fixtures Not Regulated |
| California Status      | Lawful for sale in California       |
| Title 20 / 24 Status   | Lawful for sale                     |
| California Prop 65     | Lead                                |
| RoHS Compliant         | Yes                                 |
| FCC Compliant          | Yes                                 |
| SDS Sheet              | LED_Fixture                         |

### Additional Information

|                    |                                   |
|--------------------|-----------------------------------|
| Installation Notes | Mounting Height: Up to 20 feet    |
| Includes           | Locking Hanging Hook; 6 Foot Whip |
| Warranty           | 5 Year Limited - Fixtures         |



