## SATCO NUVO

Project Name

Location Prepared By



## NUVO 65-804R2

LED UFO HIGHBAY 150W/5000K

Notes

www] 11-20-2023 01:02:4

General	
Status	Active
Fixture Type	UFO Hi-Bay
Finish	Black
Wattage	150W
Lumen Output	21750L
CCT (Kelvin)	5000K
IP Rating	IP65
Indoor or Outdoor Fixture	Indoor

Specifications	
Technology	LED
Color Temperature	Natural Light
CRI	80
Voltage	277V-480V
Beam Angle	90
Rated Hours	50000
Operating Temperature	-40C (-40F) to +45C (+113F)
Dimmable	Yes-Dimmable
Dimming Note	0-10V Dimming Only
Photocell or Sensor	Optional Add-On
Lens Material	Polycarbonate (PC)
Surge Protection	Built-in surge protection - 6KV
Weight (lb.)	6.58
Material	Die-cast Aluminum

Dimensions	
Height (in.)	8.11
Width (in.)	11.02

Compliance	
Safety Listing	cULus - Listed
Location Rating	Wet
Energy Star	No
DLC Approved	Yes
DLC ID	S-XEOBAC
NSF Approved	Yes
CA T20 / T24 Rationale	T20 Exempt - Fixtures Not Regulated
California Status	Lawful for sale in California
Title 20 / 24 Status	Lawful for sale
California Prop 65	Lead
RoHS Compliant	Yes
FCC Compliant	Yes
SDS Sheet	LED_Fixture

Additional Information	
Installation Notes	Mounting Height: Up to 25 feet
Includes	Locking Hanging Hook; 6 Foot Whip
Warranty	5 Year Limited - Fixtures



