SATCO NUVO

Project Name

Location

Prepared By



NUVO 65-805R2

LED UFO HIGHBAY 200W/4000K

Notes

www] 11-20-2023 01:02:4

| General | |
|---------------------------|------------|
| Status | Active |
| Fixture Type | UFO Hi-Bay |
| Finish | Black |
| Wattage | 200W |
| Lumen Output | 28200L |
| CCT (Kelvin) | 4000K |
| IP Rating | IP65 |
| Indoor or Outdoor Fixture | Indoor |

| Technology | LED |
|-----------------------|---------------------------------|
| Color Temperature | Cool White |
| CRI | 80 |
| Voltage | 277V-480V |
| Beam Angle | 90 |
| Rated Hours | 50000 |
| Operating Temperature | -40C (-40F) to +45C (+113F) |
| Dimmable | Yes-Dimmable |
| Dimming Note | 0-10V Dimming Only |
| Photocell or Sensor | Optional Add-On |
| Lens Material | Polycarbonate (PC) |
| Surge Protection | Built-in surge protection - 6KV |
| Weight (lb.) | 10.11 |
| Material | Die-cast Aluminum |

| Dimensions | |
|--------------|-------|
| Height (in.) | 8.11 |
| Width (in.) | 13.39 |

| Compliance | |
|------------------------|--|
| Safety Listing | cULus - Listed |
| Location Rating | Wet |
| Energy Star | No |
| DLC Approved | Yes |
| DLC ID | S-XVEN4G |
| NSF Approved | Yes |
| CA T20 / T24 Rationale | T20 Exempt - Fixtures Not Regulated |
| California Status | Lawful for sale in California |
| Title 20 / 24 Status | Lawful for sale |
| California Prop 65 | Lead |
| RoHS Compliant | Yes |
| FCC Compliant | Yes |
| SDS Sheet | LED_Fixture |

| Additional Information | |
|------------------------|--------------------------------------|
| Installation Notes | Mounting Height: Up to 30 feet |
| Includes | Locking Hanging Hook; 6 Foot Whip |
| Warranty | 5 Year Limited - Fixtures |



