

Project Name

Location

Prepared By



**Notes**

[www] 04-07-2023 14:29:35

**General**

Status	Active
Fixture Type	Vapor Tight
Finish	White and Gray
Wattage	40W/50W/60W
Lumen Output	5040L-7669L
CCT (Kelvin)	3000K/4000K/5000K
Temperature	Warm to Cool White
IP Rating	IP65
Indoor or Outdoor Fixture	Indoor and Outdoor

**Specifications**

Technology	LED
CRI	80
Voltage	120V-347V
Beam Angle	115
Rated Hours	50000
Operating Temperature	-40C (-40F) to +45C (+113F)
Dimmable	Non-Dimmable
Photocell or Sensor	Integrated Microwave Sensor
Lens Material	Polycarbonate (PC)
Surge Protection	Built-in surge protection - 2KV
Weight (lb.)	4.63
Material	Plastic

**Dimensions**

Height (in.)	3.11
Width (in.)	3.98
Length (in.)	47.24

**Compliance**

Safety Listing	cETLus - Listed
Location Rating	Wet
Energy Star	No
DLC Approved	Yes
DLC ID	S-RISVQ9
NSF Approved	Yes
CA T20 / T24 Rationale	T20 Exempt - Fixtures Not Regulated
California Status	Lawful for sale in California
Title 20 / 24 Status	Lawful for sale
California Prop 65	Lead
RoHS Compliant	Yes
FCC Compliant	Yes
Flicker Free	No
SDS Sheet	LED_Fixture

**Additional Information**

Warranty	5 Year Limited - Fixtures
----------	---------------------------