

Project Name

Location

Prepared By



Notes

[www] 01-15-2024 02:40:07

General

Status	Active
Fixture Type	Area Light
Finish	Bronze
Wattage	240W
Lumen Output	32585L
CCT (Kelvin)	5000K
Temperature	Natural Light
IP Rating	IP65
Indoor or Outdoor Fixture	Indoor; Outdoor

Specifications

Technology	LED
CRI	80
Voltage	120V-277V
Rated Hours	50000
Operating Temperature	-40C (-40F) to +45C (+113F)
Dimmable	Yes-Dimmable
Dimming Note	0-10V Dimming
Photocell or Sensor	Optional
Lens Material	Polycarbonate (PC)
Surge Protection	Built-in surge protection - 4KV
Weight (lb.)	11.93
Material	Die-cast Aluminum

Dimensions

Height (in.)	3.11
Width (in.)	12.39
Length (in.)	30.28

Compliance

Safety Listing	cULus - Certified
Location Rating	Wet
Energy Star	No
DLC Approved	Yes
DLC ID	S-4UIPTC
B.U.G. Rating	B4-U3-G4
Dark Sky Compliant	No
CA T20 / T24 Rationale	T20 Exempt - Fixtures Not Regulated
California Status	Lawful for sale in California
Title 20 / 24 Status	Lawful for sale
California Prop 65	Lead
RoHS Compliant	Yes
FCC Compliant	Yes
SDS Sheet	LED_Fixture

Additional Information

Additional Information	Powder Coated
Specification Note	Type IV Light Distribution
Includes	2-3/8 inch Slip-fitter Mount
Warranty	5 Year Limited - Fixtures

