

Project Name

Location

Prepared By



NUVO 65-860

100W LED AREA LIGHT TYPE III

Notes

[www] 05-14-2022 01:49:09

General

Status	Active
Fixture Type	Area Light
Finish	Bronze
Wattage	100W
Lumen Output	13793L
CCT (Kelvin)	4000K
Temperature	Cool White
IP Rating	IP65

Specifications

Technology	LED
CRI	80
Voltage	277V-480V
Rated Hours	50000
Operating Temperature	-40C (-40F) to a maximum of +45C (+113F)
Dimmable	Yes-Dimmable
Dimming Note	0-10V Dimming; Dimming range from 100 to less than or equal to 20 percent depending on dimmer control
Surge Protection	Built-in surge protection - 4KV
Material	Cast Aluminum

Dimensions

Height (in.)	3.11
Width (in.)	12.40
Length (in.)	20.71

Compliance

Safety Listing	cULus
Location Rating	Wet
Energy Star	No
DLC Approved	Yes
DLC ID	PL5AI0EPHH72
California Prop 65	Lead
RoHS Compliant	Yes
FCC Compliant	Yes

Additional Information

Warranty	5 Year Limited - Fixtures
----------	---------------------------