

Project Name

Location

Prepared By



NUVO 65-890

LED 35W POST TOP CCT SELECT

Notes

[www] 02-20-2020 02:53:15

General

Status	Active
Finish	Bronze
Wattage	35W
Lumen Output	4080L/4440L/4300L
CCT (Kelvin)	3000K/4000K/5000K
Temperature	Warm White to Natural Light
IP Rating	IP65

Specifications

Technology	LED
CRI	80
Voltage	120V-347V
Beam Angle	90
Rated Hours	50000
Operating Temperature	-40C (-40F) to +50C (+122F)
Dimmable	Yes-Dimmable
Dimming Note	0-10V Dimming
Lens Material	Polycarbonate (PC)
Surge Protection	Built-in surge protection - 2KV
Weight (lb.)	18.50
Material	Die Cast Aluminum

Dimensions

Height (in.)	20.59
Width (in.)	17.91

Compliance

Safety Listing	cULus
Location Rating	Wet
DLC Approved	Yes
DLC ID	S-8EN7TA
B.U.G. Rating	B2-U2-G0
Dark Sky Compliant	Yes
California Prop 65	Lead
RoHS Compliant	Yes
FCC Compliant	Yes

Additional Information

Additional Information	For International Dark Sky compliance the fixture CCT must be set to 3000K and installed in a downward facing and locked position
Specification Note	Powder Coated
Warranty	5 Year Limited - Fixtures