

Project Name

Location

Prepared By



NUVO 65-893

LED 100W POST TOP CCT SELECT

Notes

[www] 02-20-2023 02:53:15

General

Status	Active
Finish	Bronze
Wattage	100W
Lumen Output	12000L/13500/12806L
CCT (Kelvin)	3000K/4000K/5000K
Temperature	Warm White to Natural Light
IP Rating	IP65

Specifications

Technology	LED
CRI	80
Voltage	120V-347V
Beam Angle	90
Rated Hours	50000
Operating Temperature	-40C (-40F) to +50C (+122F)
Dimmable	Yes-Dimmable
Dimming Note	0-10V Dimming
Lens Material	Polycarbonate (PC)
Surge Protection	Built-in surge protection - 6KV
Weight (lb.)	18.50
Material	Die Cast Aluminum

Dimensions

Height (in.)	20.59
Width (in.)	17.91

Compliance

Safety Listing	cULus
Location Rating	Wet
DLC Approved	Yes
DLC ID	S-J760DV
B.U.G. Rating	B3-U3-G2
California Prop 65	Lead
RoHS Compliant	Yes
FCC Compliant	Yes

Additional Information

Additional Information	Powder Coated
Warranty	5 Year Limited - Fixtures